

Specifications



Eaton QBHW2050

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 50A, 22 kAIC, 120/240V , Bolt-on

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW2050
UPC	786679392805
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.1 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

Physical Attributes	
CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag

Performance Ratings	
AMPERAGE RATING	50 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous	
QUANTITY	7

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW2050

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

