



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBHW3040H 3 Pole 40A QBHW BRKR *Eaton Corp*

Catalog Number	QBHW3040H
Manufacturer	Eaton Corp
Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-Pole, 40A, 22 Kaic, 240V, Bolt-On
Weight per unit	1.1 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

dimensions	3.8000 IN X 3.2000 IN X 4.7000 IN
interrupt rating	22
Poles	3
Voltage Rating	240 V - 240 V

Descriptions

Description	3 POLE 40A QBHW BRKR
extra long description	ETN QBHW3040H 3 Pole 40 Amp QBHW B
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 40A, 22 kAIC, 240V, Bolt-on
Product Type	3 Pole 40 Amp QBHW Breaker

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679393406
Manufacturers Part Number	QBHW3040H
UPC	786679393406

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	1.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative

EnergyOtherGeneration - Conventional Energy - Conventional

EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine

Vessels and Equipment - Marine Vessels and Equipment - Other

standard

UL Listed,CSA Certified