



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QBHW3045H QBHW3045H BKR A

*Eaton Corp*

Catalog Number	QBHW3045H
Manufacturer	Eaton Corp
Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-Pole, 45 A, 22 Kaic, 240 V, Bolt-On
Weight per unit	1.2 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

### Features

dimensions	3.8000 IN X 3.3000 IN X 4.4000 IN
interrupt rating	22
Poles	3
Voltage Rating	240 V - 240 V

### Descriptions

Description	QBHW3045H BKR A
extra long description	ETN QBHW3045H Quicklag Thermal-Magn
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 45 A, 22 kAIC, 240 V, Bolt-on
Product Type	Quicklag Thermal-Magnetic CKT Breaker

### Manufacturer Information

Brand	Eaton
GTIN	00786679393420
Manufacturers Part Number	QBHW3045H
UPC	786679393420

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Weight Per each	1.15



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional  
EnergyOtherGeneration - Renewable Energy - Alternative  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment - Other

standard

CSA Certified,UL Listed