

# Specifications



## Eaton QBHW3050H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 50A, 22 kAIC, 240V, Bolt-on

### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW3050H
<b>UPC</b>	786679393451
<b>PRODUCT LENGTH/DEPTH</b>	3.8 in
<b>PRODUCT HEIGHT</b>	4.7 in
<b>PRODUCT WIDTH</b>	3.2 in
<b>PRODUCT WEIGHT</b>	1.1 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	HACR rated

## Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Three-pole
TYPE	Quicklag

## Miscellaneous

QUANTITY	32
----------	----

## Performance Ratings

AMPERAGE RATING	50 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	240 V - 240 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHW3050H</a>
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton QBHW3050H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 50A, 22 kAIC, 240V, Bolt-on

### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW3050H
<b>UPC</b>	786679393451
<b>PRODUCT LENGTH/DEPTH</b>	3.8 in
<b>PRODUCT HEIGHT</b>	4.7 in
<b>PRODUCT WIDTH</b>	3.2 in
<b>PRODUCT WEIGHT</b>	1.1 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	HACR rated

## Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Three-pole
TYPE	Quicklag

## Performance Ratings

AMPERAGE RATING	50 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	240 V - 240 V

## Miscellaneous

QUANTITY	32
----------	----

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHW3050H</a>
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

