

# Specifications



## Eaton QC2015

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 15 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable

### General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC2015
UPC	786679309339
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.65 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Physical Attributes	
CIRCUIT BREAKER TYPE	QC
CONNECTION	Cable-in/cable-out
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

Performance Ratings	
AMPERAGE RATING	15 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Miscellaneous	
OPTIONS	Non-interchangeable

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QC2015</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

