

# Specifications

## Eaton QC2020

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 20 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



### General specifications

<b>PRODUCT NAME</b>	Eaton QC thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QC2020
<b>UPC</b>	786679309377
<b>PRODUCT LENGTH/DEPTH</b>	3.8 in
<b>PRODUCT HEIGHT</b>	4.8 in
<b>PRODUCT WIDTH</b>	2.2 in
<b>PRODUCT WEIGHT</b>	0.65 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified



Powering Business Worldwide

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QC
<b>CONNECTION</b>	Cable-in/cable-out
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Industrial circuit breaker

## Performance Ratings

<b>AMPERAGE RATING</b>	20 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	T268
<b>VOLTAGE RATING</b>	120/240 V

## Miscellaneous

<b>OPTIONS</b>	Non-interchangeable
----------------	---------------------

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QC2020</a>
--------------------------------------	--

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

