

Eaton QC2050H

Catalog Number: QC2050H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 50 A, 10 kAIC, Two-pole, 240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



General specifications

Product Name	Catalog Number
Eaton QC thermal magnetic circuit breaker	QC2050H
	UPC
	786679309650
Product Length/Depth	Product Height
3.8 in	4.9 in
Product Width	Product Weight
2.2 in	0.75 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

Physical Attributes

Circuit breaker type

QC

Connection

Cable-in/cable-out

Number of poles

Two-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

240 V - 240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QC2050H](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QC2050H

Catalog Number: QC2050H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 50 A, 10 kAIC, Two-pole, 240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



General specifications

Product Name	Catalog Number
Eaton QC thermal magnetic circuit breaker	QC2050H
	UPC
	786679309650
Product Length/Depth	Product Height
3.8 in	4.9 in
Product Width	Product Weight
2.2 in	0.75 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

Physical Attributes

Circuit breaker type

QC

Connection

Cable-in/cable-out

Number of poles

Two-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

240 V - 240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QC2050H](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)