



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QC3020H Type QC BRKR 3P 20A 240VAC Maax 10kaic *Eaton Corp*

Catalog Number	QC3020H
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 20 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.8 In Overall Height, 3.8 In Overall Length, 2.9 In Overall Width
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

Features

dimensions	3.8000 IN X 2.9000 IN X 4.8000 IN
Poles	3

Descriptions

Description	TYPE QC BRKR 3P 20A 240VAC MAAX 10KAIC
extra long description	ETN QC3020H QC 3P 20A 240VAC MAAX 1
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.

Manufacturer Information

GTIN	00786679240069
UPC	786679240069

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1

Uses, Certifications, and Standards

Application	OtherDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	CSA Certified,UL Listed