

Specifications



Eaton QC3040H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 40 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC3040H
UPC	786679240144
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.9 in
PRODUCT WIDTH	3.1 in
PRODUCT WEIGHT	1.2 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QC
NUMBER OF POLES	Three-pole
TYPE	Industrial circuit breaker

Miscellaneous

OPTIONS	Non-interchangeable
----------------	---------------------

Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	240 V - 240 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QC3040H
--------------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton QC3040H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 40 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC3040H
UPC	786679240144
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.9 in
PRODUCT WIDTH	3.1 in
PRODUCT WEIGHT	1.2 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QC
NUMBER OF POLES	Three-pole
TYPE	Industrial circuit breaker

Miscellaneous

OPTIONS	Non-interchangeable
----------------	---------------------

Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	240 V - 240 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QC3040H
--------------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

