



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QC3050H Type QC BRKR 3P 50A 240VAC Max 10kaic *Eaton Corp*

Catalog Number	QC3050H
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 50 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.7 In Overall Height, 3.9 In Overall Length
Weight per unit	1.2 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

Features

dimensions	3.9000 IN X 3.2000 IN X 4.7000 IN
Poles	3

Descriptions

Description	TYPE QC BRKR 3P 50A 240VAC MAX 10KAIC
extra long description	ETN QC3050H TYPE QC BREAKER 3P 50A
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.

Manufacturer Information

GTIN	00786679240182
UPC	786679240182

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1.15

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional Energy Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Datacenters - IT Space: CI and Hyper Converged Other
standard	UL Listed, CSA Certified