



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QC3050H Type QC BRKR 3P 50A 240VAC Max 10kaic *Eaton Corp*

Catalog Number	QC3050H
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 50 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.7 In Overall Height, 3.9 In Overall Length
Weight per unit	1.2 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

### Features

dimensions	3.9000 IN X 3.2000 IN X 4.7000 IN
Poles	3

### Descriptions

Description	TYPE QC BRKR 3P 50A 240VAC MAX 10KAIC
extra long description	ETN QC3050H TYPE QC BREAKER 3P 50A
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.

### Manufacturer Information

GTIN	00786679240182
UPC	786679240182

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Package	8
Weight Per each	1.15

### Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional Energy Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Datacenters - IT Space: CI and Hyper Converged Other
standard	UL Listed, CSA Certified