

# Eaton QC3070H

Catalog Number: QC3070H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 70 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QC thermal magnetic circuit breaker	QC3070H
	UPC
	786679240243
<b>Product Length/Depth</b>	<b>Product Height</b>
3.8 in	4.9 in
<b>Product Width</b>	<b>Product Weight</b>
3.2 in	1.2 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed

## Physical Attributes

### Circuit breaker type

QC

### Connection

Cable-in/cable-out

### Number of poles

Three-pole

### Type

Industrial circuit breaker

## Performance Ratings

### Amperage Rating

70A

### Interrupt rating

10 kAIC

### Trip Type

Thermal-magnetic

### Voltage rating

240 V - 240 V

## Miscellaneous

### Options

Non-interchangeable

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QC3070H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QC3070H

Catalog Number: QC3070H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 70 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QC thermal magnetic circuit breaker	QC3070H
	UPC
	786679240243
<b>Product Length/Depth</b>	<b>Product Height</b>
3.8 in	4.9 in
<b>Product Width</b>	<b>Product Weight</b>
3.2 in	1.2 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed

## Physical Attributes

### Circuit breaker type

QC

### Connection

Cable-in/cable-out

### Number of poles

Three-pole

### Type

Industrial circuit breaker

## Performance Ratings

### Amperage Rating

70A

### Interrupt rating

10 kAIC

### Trip Type

Thermal-magnetic

### Voltage rating

240 V - 240 V

## Miscellaneous

### Options

Non-interchangeable

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QC3070H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)