

Eaton QCR1020

Catalog Number: QCR1020

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Non-interchangeable



General specifications

Product Name	Catalog Number
Eaton QCR thermal magnetic circuit breaker	QCR1020
	UPC
	786679144060
Product Length/Depth	Product Height
4.7 in	1.2 in
Product Width	Product Weight
3.1 in	0.2 lb
Warranty	Compliances
1 year	HACR Rated
Certifications	Catalog Notes
UL Listed CSA Certified	Standard breaker terminals are box type lugs. Switching duty rated for fluorescent lighting applications.

Physical Attributes

Circuit breaker type

QCR

Connection

Cable-in/cable-out

Mounting Method

Rear

Number of poles

Single-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

120/240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QCR1020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia