

# Specifications



## Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QCR
<b>CONNECTION</b>	Cable-in/cable-out
<b>MOUNTING METHOD</b>	Rear
<b>NUMBER OF POLES</b>	Two-pole
<b>TERMINALS</b>	Fixed
<b>TYPE</b>	Industrial circuit breaker

### General specifications

<b>PRODUCT NAME</b>	Eaton QCR thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QCR2030
<b>UPC</b>	786679144343
<b>PRODUCT LENGTH/DEPTH</b>	4.6 in
<b>PRODUCT HEIGHT</b>	1.2 in
<b>PRODUCT WIDTH</b>	3.3 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	HACR Rated
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	Standard breaker terminals are box type lugs.



Powering Business Worldwide

# Specifications



## Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QCR
<b>CONNECTION</b>	Cable-in/cable-out
<b>MOUNTING METHOD</b>	Rear
<b>NUMBER OF POLES</b>	Two-pole
<b>TERMINALS</b>	Fixed
<b>TYPE</b>	Industrial circuit breaker

### General specifications

<b>PRODUCT NAME</b>	Eaton QCR thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QCR2030
<b>UPC</b>	786679144343
<b>PRODUCT LENGTH/DEPTH</b>	4.6 in
<b>PRODUCT HEIGHT</b>	1.2 in
<b>PRODUCT WIDTH</b>	3.3 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	HACR Rated
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	Standard breaker terminals are box type lugs.



Powering Business Worldwide