

Specifications



Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

Physical Attributes

CIRCUIT BREAKER TYPE	QCR
CONNECTION	Cable-in/cable-out
MOUNTING METHOD	Rear
NUMBER OF POLES	Two-pole
TERMINALS	Fixed
TYPE	Industrial circuit breaker

General specifications

PRODUCT NAME	Eaton QCR thermal magnetic circuit breaker
CATALOG NUMBER	QCR2030
UPC	786679144343
PRODUCT LENGTH/DEPTH	4.6 in
PRODUCT HEIGHT	1.2 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
COMPLIANCES	HACR Rated
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Standard breaker terminals are box type lugs.



Powering Business Worldwide