

Eaton QCR2060

Catalog Number: QCR2060

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 60 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

General specifications



Product Name	Catalog Number
Eaton QCR thermal magnetic circuit breaker	QCR2060
	UPC
	786679144466
Product Length/Depth	Product Height
4.6 in	1.2 in
Product Width	Product Weight
3.1 in	0.25 lb
Warranty	Compliances
1 year	HACR Rated
Certifications	Catalog Notes
CSA Certified UL Listed	Standard breaker terminals are box type lugs.

Physical Attributes

Circuit breaker type

QCR

Connection

Cable-in/cable-out

Mounting Method

Rear

Number of poles

Two-pole

Terminals

Fixed

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

60 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

120/240 V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QCR2060](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)