



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QHE4X32T8UNVISNS *Delisted* Electronic Ballast *Sylvania-Ledvance*

Catalog Number	QHE4X32T8UNVISNS
Manufacturer	Sylvania-Ledvance
Description	OBS49857 4 Lamp 32WT8 High Efficiency Instant Start Electronic Ballast, Universal Voltage, Normal Ballast Factor, 10 PK
Weight per unit	0.9500 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	120
Ballast Factor	0.88
Minimum Starting Temperature	-20.000000000000000
Number of Lamps	4
Power Factor	>0.97
start type	Instant Start
total harmonic distortion	<10
Voltage	120.00 - 277.00 V

Dimensions and Weight

Height	1.1810000000000000
Length	9.4690000000000000
Width	1.6810000000000000

Descriptions

Description	*DELISTED* ELECTRONIC BALLAST
extra long description	SYL QHE-4X32T8/UNV-ISN-SC/49857 QHE
Long Description	OBS49857 4 lamp 32wT8 High Efficiency Instant Start electronic ballast, universal voltage, normal ballast factor, 10 pk
Product Type	QHE4X32T8UNVISNSC 10/CS 1/Sku
Special Features	NO

Manufacturer Information

Brand	OSRAM
GTIN	00046135498572
Manufacturers Part Number	QHE-4X32T8/UNV-ISN-SC/49857
UPC	046135498572

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts And Lighting Controls

Packaging

Carton	1
Package	10
Weight Per each	0.95