



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ROS250 1/0-250 Awg Direct Burial "Cold Roll-On" Splice

Nsi Industries

Catalog Number	ROS250
Manufacturer	Nsi Industries
Description	Easy-Splice Roll On, Black Insulation Color, Easy Splice Sleeve;Sealant Strip, -40 °C Operating Temperature, +90 °C Operating Temperature, 4.5 In Overall Length, 1000 V, 0.26 LB
Weight per unit	0.2600 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	1/0 AWG-250 MCM
Cable Type	Class A-B
insulation	EPDM Elastomer
Voltage Rating	1000 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
-------	-------

Descriptions

Description	1/0-250 AWG DIRECT BURIAL "COLD ROLL-ON" SPLICE
extra long description	NSI ROS-250 Easy-Splice Roll On 250
Special Features	Easy Roll-On Way To Insulate And Seal Cable - Made Of EPDM Elastomer

Manufacturer Information

GTIN	00662381123367
UPC	662381123367

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Roll-On Splice Kits

Packaging

Carton	2
Weight Per each	0.26

Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature standard	-40 C To 90 C ANSI C119.1-1986 Qualified, UL 486D