



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



R406111A 18/6 Oa Foil SHLD *Southwire Company*

| | |
|------------------|--|
| Catalog Number | R406111A |
| Manufacturer | Southwire Company |
| Description | 18 Awg 6/C Stranded Shielded CMR/CL3R/FPLR Cable |
| Weight per unit | 0.0480 (lbs/ft) |
| Product Category | Line Construction Material |

Features

| | |
|----------------------|----------|
| amperage rating | CL3 |
| Conductor Size | 18 |
| core | SHIELDED |
| Number of Conductors | 6 |
| outside diameter | 0.23 |
| Resistance | 6.92 |
| strands | 7 |
| Voltage Rating | 300 |

Material, Color, and Finish

| | |
|---------------------|------|
| Color | Gray |
| Conductor Material | BC |
| Finish | BULK |
| Insulation Material | PVC |
| Jacket Material | PVC |

Descriptions

| | |
|------------------------|--|
| Construction | CABLE |
| Description | 18/6 OA FOIL SHLD |
| extra long description | SWC R40611-1A 18 AWG 6/C STRANDED S |
| Long Description | 18 AWG 6/C STRANDED SHIELDED CMR/CL3R/FPLR CABLE |
| Product Type | 18 Awg 6/C Stranded Shielded CMR/CL3R/FPLR Cable |
| Special Features | CL3R |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cables & Cords |
| GTIN | 00032886883019 |
| Manufacturers Part Number | R40611-1A |
| UPC | 032886883019 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------|
| Category Description | ELECTRONIC CABLE |
| Type | CMR |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 1000 |
| Weight | 48 |
| Weight Per foot | 0.048 |

Uses, Certifications, and Standards

| | |
|--------------------|--------|
| Application | CL3 |
| standard | UL 444 |
| Temperature Rating | 60 |