

# Eaton RACH24L125I

Catalog Number: RACH24L125I

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main lug only, 125 A, size group a, Cover height: 33 in, Cover width: 24 in, NEMA 1, CH, Surface, flush, 24 Circuits, Single-phase, 0.75 in, #4-2/0 AWG

## General specifications



Photo is representative

### Product Name

Eaton CH retrofit kit

### UPC

786685211060

### Product Height

30 in

### Product Weight

1 lb

### Certifications

UL 67

### Catalog Number

RACH24L125I

### Product Length/Depth

6 in

### Product Width

22 in

### Warranty

1 year

### Catalog Notes

Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.

## Product specifications

### Type

Retrofit kit

### Amperage Rating

125 A

### Main circuit breaker

CH

### Mounting

Surface, flush

### Number of circuits

24

### Phase

Single-phase

### Wire size

#4-2/0 AWG

### Box size

Retro size group a

### Cover height

33

### Cover width

24

### Enclosure

NEMA 1

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - RACH24L125I](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)