

Specifications

Eaton RACH24L125I



Photo is representative

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main lug only, 125 A, size group a, Cover height: 33 in, Cover width: 24 in, NEMA 1, CH, Surface, flush, 24 Circuits, Single-phase, 0.75 in, #4-2/0 AWG

General specifications

PRODUCT NAME	Eaton CH retrofit kit
CATALOG NUMBER	RACH24L125I
UPC	786685211060
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	30 in
PRODUCT WIDTH	22 in
PRODUCT WEIGHT	1 lb
WARRANTY	1 year
CERTIFICATIONS	UL 67
CATALOG NOTES	Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.



Product specifications

TYPE Retrofit kit

Resources

MULTIMEDIA [AFCI Educational Video](#)

AMPERAGE RATING	125 A
MAIN CIRCUIT BREAKER	CH
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	24
PHASE	Single-phase
WIRE SIZE	#4-2/0 AWG
BOX SIZE	Retro size group a
COVER HEIGHT	33
COVER WIDTH	24
ENCLOSURE	NEMA 1

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - RACH24L125I
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

