



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCC217 12-10 Butt Splice Bulk

Abb Installation Products, Inc

Catalog Number	RCC217
Manufacturer	Abb Installation Products, Inc
Description	Expanded Vinyl Insulated Butt Splice, Length 1.31 Inches, Width .29 Inches, Maximum Insulation Diameter .210, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated, Mini-Pack, 1, 000 Pack
Weight per unit	0.0080 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Yellow
Finish	Electro -Tin Plated

Descriptions

Description	12-10 BUTT SPLICE BULK
extra long description	ABB RCC217 INS VINYL BUTT SPLICE, 1
Long Description	Expanded Vinyl Insulated Butt Splice, Length 1.31 Inches, Width .29 Inches, Maximum Insulation Diameter .210, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, Mini-Pack, 1,000 Pack
Product Type	Ins Vinyl Butt Splice, 12-10 Len 1.
Special Features	In butt splices, the wires are butted together and crimped at each end of the splice. These splices are color-coded according to wire size

Manufacturer Information

Brand	Sta-Kon
GTIN	00786210820538
Manufacturers Part Number	RCC217
UPC	786210820538

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Vinyl Insulated Butt Splice

Packaging

Carton	500
Package	5000
Weight Per each	0.008



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard	UL E9809 / UL E9809
Temperature Rating	105 C