



TWO SINGLE POLE SWITCHES, IVORY

RCD111 | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.



- Part of the all-new radiant® collection.
- Unique "Up/Down" switches match the look and feel of radiant paddle switches.
- Easy-to-use oversized main switch for primary load.
- Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.
- Impact-resistant face and body.
- Full wraparound metal strap, commercial grade with lock-in tabs.
- All screws are tri-drive.
- Patented split circuit tab - easily accessible, and can be reinstalled without a tool.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Largest breadth of 15 amp offering.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Combination
Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121704

CONSTRUCTION INFORMATION

Component 4: 78500705485

DIMENSIONS

Depth (US): 1.43"
Height (US): 3.81"
Width (US): 1.29

TECHNICAL INFORMATION

Amps: 15A
Volts: 120VAC



TWO SINGLE POLE SWITCHES, IVORY

RCD111 | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.



- Part of the all-new radiant® collection.
- Unique "Up/Down" switches match the look and feel of radiant paddle switches.
- Easy-to-use oversized main switch for primary load.
- Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.
- Impact-resistant face and body.
- Full wraparound metal strap, commercial grade with lock-in tabs.
- All screws are tri-drive.
- Patented split circuit tab - easily accessible, and can be reinstalled without a tool.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Largest breadth of 15 amp offering.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Combination
Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121704

CONSTRUCTION INFORMATION

Component 4: 78500705485

DIMENSIONS

Depth (US): 1.43"
Height (US): 3.81"
Width (US): 1.29

TECHNICAL INFORMATION

Amps: 15A
Volts: 120VAC