



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RCD33I Radiant 2 SW SP/3WAY + SP/3WAY Iv *Pass & Seymour/Legrand*

Catalog Number	RCD33I
Manufacturer	Pass & Seymour/Legrand
Description	15A 120V Radiant Combination (2) Single Pole/3-Way Switches, Ivory
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

### Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	120
media	Yes
operating cycles	50,000 cycles minimum, resistive, inductive, tungstun filament lamp load
Poles	3
Voltage Rating	120

### Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--

### Descriptions

Description	RADIANT 2 SW SP/3WAY + SP/3WAY IV
extra long description	P&S RCD33I RADIANT 2 SW, SP/3WAY +
Long Description	15A 120V Radiant Combination (2) Single Pole/3-Way Switches, Ivory
Product Type	Radiant 2 SW, SP/3WAY + SP/3WAY I
Special Features	The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. Unique "Up/Down" switches match the look and feel of radiant paddle switches.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007054941
Manufacturers Part Number	RCD33I
UPC	785007054941

### Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Two Single Pole/3-Way Switches



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	12
Weight Per each	0.2083

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	cULus, UL Listed