



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD33W Radiant 2 SW SP/3WAY + SP/3WAY WH

Pass & Seymour/Legrand

Catalog Number	RCD33W
Manufacturer	Pass & Seymour/Legrand
Description	Two Single Pole Switch, 3 Poles, 3 Ways, 15 A, 120/125 V Ac, Stainless Steel, White, Rocker Actuator, Box Mount, 1.29 (L) X 1.59 (W) X 3.81 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.21 LB
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	15 Amp, 120/125 VAC
media	Yes
Number of Gangs	1.0
Number of Switches	2.0
operating cycles	50000
Poles	1, 3-Way
Switch Type	Push
Voltage	120.0 V
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	------------------------------------------

Descriptions

Description	RADIANT 2 SW SP/3WAY + SP/3WAY WH
extra long description	P&S RCD33W RADIANT 2 SW, SP/3WAY +

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007054972
UPC	785007054972

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	SWITCH

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.2083

Uses, Certifications, and Standards

environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature standard	Maximum continuous +115°C, minimum -40°C UL, CULUS, cULus, UL Listed