



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD38TRLA Radiant SP/3WAY SW+15A TR Outlet La *Pass & Seymour/Legrand*

Catalog Number	RCD38TRLA
Manufacturer	Pass & Seymour/Legrand
Description	15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, Light Almond
Weight per unit	0.2080 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	125
operating cycles	50,000 cycles minimum, resistive, inductive, tungstun filament lamp load
Poles	3
Voltage Rating	125

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--

Descriptions

Description	RADIANT SP/3WAY SW+15A TR OUTLET LA
extra long description	P&S RCD38TRLA RADIANT SP/3WAY SW+15
Long Description	15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, Light Almond
Product Type	Radiant SP/3WAY SW+15A TR Outlet La
Special Features	The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007055061
Manufacturers Part Number	RCD38TRLA
UPC	785007055061

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Single Pole/3-Way Switch & Tamper-Resistant Outlet



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.208

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	cULus, UL Listed