



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD38TRW Radiant SP/3WAY SW+15A TR Outlet WH *Pass & Seymour/Legrand*

Catalog Number	RCD38TRW
Manufacturer	Pass & Seymour/Legrand
Description	15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, White
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	125
indoor/outdoor	Indoor
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Outlet Type	Tamper-Resistant
Poles	Single Pole
Switch Type	Push
Voltage	120.0 V
Voltage Rating	125

Material, Color, and Finish

Color	White
Finish	Matte

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--

Descriptions

Description	RADIANT SP/3WAY SW+15A TR OUTLET WH
extra long description	P&S RCD38TRW RADIANT SP/3WAY SW+15A
Features	Combination, Locator Light
Long Description	15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, White
Product Type	Radiant SP/3WAY SW+15A TR Outlet WH
Special Features	Single Pole 3-Way Switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007055085
Manufacturers Part Number	RCD38TRW
UPC	785007055085

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Switch, Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	12
Weight Per each	0.2083

Uses, Certifications, and Standards

Application	Residential
environmental conditions	Flammability Rating: UL 94 V2
Mounting	BOX
nema rating	15A
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	CULUS, UL, cULus, UL Listed