



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RCD38TRW Radiant SP/3WAY SW+15A TR Outlet WH

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | RCD38TRW  |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | A Step Up From Ordinary, This Combination Switch and Outlet From The Radiant® Collection Provides Convenience and Flexibility, As Well As Style. Operable In Both Single-Pole and 3-Way Applications, You Can Use It Alone to Control One Light or Fixture, or Use With Another 3-Way Switch For Controlling The Light From Two Locations. Also Includes A Tamper-Resistant Outlet For Safe Access to The Basic Power Every Home Needs. Part Of The Radiant® Collection, It Features Clean Lines and A Smooth Finish For A Soph |
| Weight per unit  | 0.2083 (lbs/each)   |
| Product Category | Gen Purpose Switches  |

### Features

|                       |                     |
|-----------------------|---------------------|
| actuator              | Rocker switch       |
| amperage rating       | 15                  |
| Contact Configuration | 15A                 |
| Contact Rating        | 15 Amp, 120/125 VAC |
| indoor/outdoor        | Indoor              |
| media                 | Yes                 |
| Mounting Type         | Box                 |
| Number of Gangs       | 1.0                 |
| Number of Switches    | 1.0                 |
| operating cycles      | 50000               |
| Outlet Type           | Tamper-Resistant    |
| Poles                 | 3-Way, 1            |
| Switch Type           | Push                |
| Voltage               | 120.0 V             |
| Voltage Rating        | 125                 |
| Wire Size             | #14 - #10 Awg       |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | White |
| Finish | Matte |

### Dimensions and Weight

|      |  |
|------|--|
| Size | Depth 1.43" x Width 1.29" x Height 3.81" |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | RADIANT SP/3WAY SW+15A TR OUTLET WH   |
| extra long description | P&S RCD38TRW RADIANT SP/3WAY SW+15A   |
| Features               | Locator Light, Combination  |
| Long Description       | A step up from ordinary, this combination switch and outlet from the radiant® Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant® Collection, it features clean lines and a smooth finish for a soph |
| Product Type           | Radiant SP/3WAY SW+15A TR Outlet WH   |
| Special Features       | Single Pole 3-Way Switch  |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007055085         |
| Manufacturers Part Number | RCD38TRW               |
| UPC                       | 785007055085           |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type                 | Switch, Outlet     |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 12     |
| Weight Per each | 0.2083 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Residential                              |
| environmental conditions | Flammability Rating: UL 94 V2            |
| Mounting                 | BOX                                      |
| nema rating              | 15A                                      |
| Operating Temperature    | Maximum continuous +115°C, minimum -40°C |
| standard                 | CULUS, UL, cULus, UL Listed              |