

Specifications

Eaton REN-30

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V



General specifications

| | |
|----------------------|--------------------------------|
| PRODUCT NAME | Eaton Bussmann series REN fuse |
| CATALOG NUMBER | REN-30 |
| UPC | 051712100304 |
| PRODUCT LENGTH/DEPTH | 2 in |
| PRODUCT HEIGHT | 0.56 in |
| PRODUCT WIDTH | 0.56 in |
| PRODUCT WEIGHT | 0.55 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | Not Applicable |

| Electrical rating | |
|-------------------|---------|
| AMPERAGE RATING | 30 A |
| INTERRUPT RATING | 10 kAIC |
| VOLTAGE RATING | 250 V |

| General information | |
|---------------------|---|
| CLASS | Class H |
| CONNECTION | Ferrule end x ferrule end |
| FUSE INDICATOR | Non-indicating |
| QUANTITY | 10 |
| SPECIAL FEATURES | Super lag, time lag, non current-limiting |

| Physical details | |
|------------------|----------|
| PACKAGING TYPE | Standard |

| Resources | |
|-------------------------------|--|
| CATALOGS | Bussmann series complete full line catalog no. 1007 |
| | Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses |
| | REN-30~SUPER LAG RENEWABLE FUSE 30/250 |
| MULTIMEDIA | Bussmann series Fuseology |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - REN-30 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications

Eaton REN-30

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V



General specifications

| | |
|----------------------|--------------------------------|
| PRODUCT NAME | Eaton Bussmann series REN fuse |
| CATALOG NUMBER | REN-30 |
| UPC | 051712100304 |
| PRODUCT LENGTH/DEPTH | 2 in |
| PRODUCT HEIGHT | 0.56 in |
| PRODUCT WIDTH | 0.56 in |
| PRODUCT WEIGHT | 0.55 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | Not Applicable |

| Electrical rating | |
|-------------------|---------|
| AMPERAGE RATING | 30 A |
| INTERRUPT RATING | 10 kAIC |
| VOLTAGE RATING | 250 V |

| General information | |
|---------------------|---|
| CLASS | Class H |
| CONNECTION | Ferrule end x ferrule end |
| FUSE INDICATOR | Non-indicating |
| QUANTITY | 10 |
| SPECIAL FEATURES | Super lag, time lag, non current-limiting |

| Physical details | |
|------------------|----------|
| PACKAGING TYPE | Standard |

| Resources | |
|-------------------------------|--|
| CATALOGS | Bussmann series complete full line catalog no. 1007 |
| | Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses |
| | REN-30~SUPER LAG RENEWABLE FUSE 30/250 |
| MULTIMEDIA | Bussmann series Fuseology |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - REN-30 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

