



Powering Business Worldwide

pe.eaton.com

Rotary Dimmer

RI06P-W

UPC:032664699023

Dimensions:

- **Height:** 4.75 IN
- **Length:** 2.3 IN
- **Width:** 3.06 IN

Weight: .24 LB

Warranties: No Data

Specifications:

- **Special Features:** Power failure memory, with preset
- **Allowable Wire Size:** #16 AWG
- **Amperage Rating:** 5A
- **Mounting Type:** Flush
- **Voltage Rating:** 120V
- **Wiring Method:** Wire lead
- **Closure Type:** Maintained
- **Color:** White
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** Incandescent, halogen
- **Operating Temperature:** 0° to 40°C
- **Switch Type:** Single-pole, three-way
- **Material:** Polycarbonate
- **Wattage:** 600W

Supporting documents: No Data

Certifications:

- NOM
- cULus Listed

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Rotary Dimmer

RI06P-W

UPC:032664699023

Dimensions:

- **Height:** 4.75 IN
- **Length:** 2.3 IN
- **Width:** 3.06 IN

Weight: .24 LB

Warranties: No Data

Specifications:

- **Special Features:** Power failure memory, with preset
- **Allowable Wire Size:** #16 AWG
- **Amperage Rating:** 5A
- **Mounting Type:** Flush
- **Voltage Rating:** 120V
- **Wiring Method:** Wire lead
- **Closure Type:** Maintained
- **Color:** White
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** Incandescent, halogen
- **Operating Temperature:** 0° to 40°C
- **Switch Type:** Single-pole, three-way
- **Material:** Polycarbonate
- **Wattage:** 600W

Supporting documents: No Data

Certifications:

- NOM
- cULus Listed

Product compliance: No Data



