

# Eaton RJDN250

Catalog Number: RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface



## General specifications

|                                |  |
|--------------------------------|--|
| <b>Product Name</b>            | <b>Catalog Number</b>  |
| Eaton enclosed circuit breaker | RJDN250  |
| <b>UPC</b>                     | <b>Product Length/Depth</b>  |
| 786679256145                   | 10.22 in   |
| <b>Product Height</b>          | <b>Product Width</b>   |
| 37.5 in                        | 11.88 in   |
| <b>Product Weight</b>          | <b>Warranty</b>  |
| 37 lb                          | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>Certifications</b>          | <b>Catalog Notes</b>   |
| UL Listed<br>CSA Certified     | With Knockouts   |

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

125-250A

### Circuit breaker type

JD, JDB, HJD, JDC

### Enclosure

NEMA 3R

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Brochures

[Customized Solutions - Customized Service](#)

### Drawings

[Dimension Sheet RJDN250](#)

### Specifications and datasheets

[Enclosed Circuit Breakers - Technical Data](#)

[Eaton Specification Sheet - RJDN250](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton RJDN250

Catalog Number: RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface



## General specifications

|                                |  |
|--------------------------------|--|
| <b>Product Name</b>            | <b>Catalog Number</b>  |
| Eaton enclosed circuit breaker | RJDN250  |
| <b>UPC</b>                     | <b>Product Length/Depth</b>  |
| 786679256145                   | 10.22 in   |
| <b>Product Height</b>          | <b>Product Width</b>   |
| 37.5 in                        | 11.88 in   |
| <b>Product Weight</b>          | <b>Warranty</b>  |
| 37 lb                          | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>Certifications</b>          | <b>Catalog Notes</b>   |
| UL Listed<br>CSA Certified     | With Knockouts   |

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

125-250A

### Circuit breaker type

JD, JDB, HJD, JDC

### Enclosure

NEMA 3R

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Brochures

[Customized Solutions - Customized Service](#)

### Drawings

[Dimension Sheet RJDN250](#)

### Specifications and datasheets

[Enclosed Circuit Breakers - Technical Data](#)

[Eaton Specification Sheet - RJDN250](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)