



## RL4LS9FSD2W1EWH 4" 11W Led Retro 27K/3K/35K/4K/5K D2W 600/900LM

Cooper Lighting Solutions

Catalog Number	RL4LS9FSD2W1EWH
Manufacturer	Cooper Lighting Solutions
Description	4-Inch Recessed Led Retrofit Module, 600/900 Selectable Lumens (Nominal), 90 Cri, Selectable CCT With D2W Option, 120V 60HZ, Le & Te Phase Cut 5% Dimming, Matte White Flange.
Weight per unit	0.5900 (lbs/each)
Product Category	Lighting

### Features

Fixture Type	Retrofit Kit
Lamp Type	LED

### Dimensions and Weight

Size	5.24 IN Length 3.23 IN Width 5.31 IN Height
------	---

### Descriptions

Description	4" 11W LED RETRO 27K/3K/35K/4K/5K D2W 600/900LM
extra long description	CLS RL4LS9FSD2W1EWH 4" RL, 600/900L
Long Description	4-inch recessed LED retrofit module, 600/900 selectable lumens (nominal), 90 CRI, selectable CCT with D2W option, 120V 60Hz, LE & TE phase cut 5% dimming, matte white flange.
Product Type	4" RL, 600/900LM, 5CCT, D2W, 120V
Special Features	Available in 4" and 6"

### Manufacturer Information

Brand	HALO
GTIN	00080083257683
Manufacturers Part Number	RL4LS9FSD2W1EWH
UPC	080083257683

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RL4 LED

### Packaging

Carton	1
Package	4
Weight Per each	0.59



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

lighting

Mounting

Recessed

standard

California Title 20;California Title 24;Energy Star;IC Rated;IECC  
Compliant;RoHS Compliant;UL Listed