



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RLT12 1/2" Met L/T, Non UI 500' *Southwire Company*

Catalog Number	RLT12
Manufacturer	Southwire Company
Description	Non-UI Liquid-Tuff™ Liquidtight Conduit, Type VF, 6100 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1/2 Inch Diameter, 1000 Foot Reel
Weight per unit	0.2600 (lbs/ft)
Product Category	Flexible Metallic Conduit

Features

Inside Diameter	0.622/0.642
Material	Steel
outside diameter	0.820/0.840

Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

Dimensions and Weight

Length	1000
--------	------

Descriptions

Description	1/2" MET L/T, NON UL 500'
extra long description	AFC 6102-60-00 1/2 LIQUID-TUFF VF L
Features	LIQUID-TUFF™ Liquidtight, Flexible Steel Conduit, Type VF is a general purpose Non-UL raceway that is oil and sunlight resistant. Designed to be used for specific applications where Underwriters Laboratories Inc. (UL) or other agency approvals are not required.
Long Description	Non-UL LIQUID-TUFF™ Liquidtight Conduit, Type VF, 6100 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1/2 inch Diameter, 1000 Foot Reel
Product Type	1/2 Liquid-Tuff VF LT 1000 RL
Short Description	1/2 LIQUID-TUFF VF LT 1000 RL

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680119568
Manufacturers Part Number	6102-60-00
UPC	077680119568



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

Trade Size

Trade Size	1/2
------------	-----

Packaging

Carton	500
Package	1000
Weight	0.28
Weight Per foot	0.26

Uses, Certifications, and Standards

Application	600 V and lower circuits.
Temperature Rating	140