



## 120V SINGLE POLE VACANCY SENSOR, TRI-COLOR

RRW600VTC | [radiant](#)

### FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

This sensor replaces a standard light or fan single pole switch and is ideal for bedrooms and baths. Includes three interchangeable face plates.

radiant® Screwless Wall Plate not included.



- Part of the all-new radiant® collection.
- Lighted switch for visibility in darkened rooms.
- Manual-ON feature.
- Adjustable time delay of 30 seconds to 30 minutes.
- No neutral required.
- Low-profile styling with uniform color-matched lens and device.
- Coverage: 180 degrees, max. 600 ft.2 (56m2)
- Works with most common residential lighting types.
- Load: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond)  
Number Of Poles: 1

Number Of Wires: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

UN SPSC: 39121502

#### CONSTRUCTION INFORMATION

Component 4: 78500749658

#### DIMENSIONS

Depth (US): 1.88"

Height (US): 2.63"

Width (US): 1.69"

#### TECHNICAL INFORMATION

Volts (AC): 120VAC, 60Hz

Watts: 0-600W All

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA



## 120V SINGLE POLE VACANCY SENSOR, TRI-COLOR

RRW600VTC | [radiant](#)

### FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

This sensor replaces a standard light or fan single pole switch and is ideal for bedrooms and baths. Includes three interchangeable face plates.

radiant® Screwless Wall Plate not included.



- Part of the all-new radiant® collection.
- Lighted switch for visibility in darkened rooms.
- Manual-ON feature.
- Adjustable time delay of 30 seconds to 30 minutes.
- No neutral required.
- Low-profile styling with uniform color-matched lens and device.
- Coverage: 180 degrees, max. 600 ft.2 (56m2)
- Works with most common residential lighting types.
- Load: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond)  
Number Of Poles: 1

Number Of Wires: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

UN SPSC: 39121502

#### CONSTRUCTION INFORMATION

Component 4: 78500749658

#### DIMENSIONS

Depth (US): 1.88"

Height (US): 2.63"

Width (US): 1.69"

#### TECHNICAL INFORMATION

Volts (AC): 120VAC, 60Hz

Watts: 0-600W All

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA