

Specifications



Eaton RSPF2403SA2A

Eaton Surge Protection Device for sub-panel, RSPF Series, F Frame, 120/208Y, 127/220Y, 240D rating, integrated, Basic feature package plus filtering, Direct Bus Mounted

General specifications

PRODUCT NAME	Eaton RSPF surge protection device
CATALOG NUMBER	RSPF2403SA2A
UPC	786689030605
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	7.5 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	2.38 lb
WARRANTY	2 year
CERTIFICATIONS	UL 1449 UL Listed



Powering Business Worldwide

Product specifications

TYPE	SPD
SPECIAL FEATURES	Meets or exceeds the requirements specified in IBC @2006, CBC2007, and UBC@Zone 4

Resources

CATALOGS	Power Distribution and Control Assemblies, SPD, Power Conditioning, PF Capacitors and Harmonic Filters, Volume 3, Tab 2
-----------------	---

ACCESSORIES	Basic Plus Filtering
FREQUENCY RATING	50/60 Hz
NOMINAL DISCHARGE CURRENT	20 kA
USED WITH	Direct bus mounted
PHASE	Three-phase
OPERATING TEMPERATURE	-40 to 60 °C

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - RSPF2403SA2A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Eaton RSPF2403SA2A

Eaton Surge Protection Device for sub-panel, RSPF Series, F Frame, 120/208Y, 127/220Y, 240D rating, integrated, Basic feature package plus filtering, Direct Bus Mounted

General specifications

PRODUCT NAME	Eaton RSPF surge protection device
CATALOG NUMBER	RSPF2403SA2A
UPC	786689030605
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	7.5 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	2.38 lb
WARRANTY	2 year
CERTIFICATIONS	UL 1449 UL Listed



Powering Business Worldwide

Product specifications

TYPE	SPD
SPECIAL FEATURES	Meets or exceeds the requirements specified in IBC @2006, CBC2007, and UBC@Zone 4

Resources

CATALOGS	Power Distribution and Control Assemblies, SPD, Power Conditioning, PF Capacitors and Harmonic Filters, Volume 3, Tab 2
-----------------	---

ACCESSORIES	Basic Plus Filtering
FREQUENCY RATING	50/60 Hz
NOMINAL DISCHARGE CURRENT	20 kA
USED WITH	Direct bus mounted
PHASE	Three-phase
OPERATING TEMPERATURE	-40 to 60 °C

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - RSPF2403SA2A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

