



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RV108Q Highland Vinyl Ins Ring Term, 12-10awg *Minnesota Mining (3M)*

Catalog Number	RV108Q
Manufacturer	Minnesota Mining (3M)
Description	3M™ Highland™ Ring Tongue Terminal Ensures An Ideal Fit While Offering Reliable and Safe Performance. The Terminal Has A Vinyl-Insulated, Butted-Seam Barrel and Withstands Temperatures Of -40 to 221 Degrees F (-40 to 105 Degrees C). Electrolytic Copper Construction Offers Good Conductivity and A Tin-Plated Finish Resists Corrosion.
Weight per unit	0.0119 (lbs/each)
Product Category	Small Terminals & Connectors

### Descriptions

Description	HIGHLAND VINYL INS RING TERM, 12-10AWG
extra long description	3M 7000133675 3M™ Highland™ Vinyl I
Features	A ring is the standard style of tongue. The safest and most reliable; it cannot be removed unless mounting screw is removed.
Long Description	3M™ Highland™ Ring Tongue Terminal ensures an ideal fit while offering reliable and safe performance. The terminal has a vinyl-insulated, butted-seam barrel and withstands temperatures of -40 to 221 degrees F (-40 to 105 degrees C). Electrolytic copper construction offers good conductivity and a tin-plated finish resists corrosion.
Product Type	3M™ Highland™ Vinyl Insulated Butted Seam Ring Tongues

### Manufacturer Information

Brand	Scotchlok
GTIN	00051128600375
Manufacturers Part Number	RV108Q
UPC	051128600375

### Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	RING

### Packaging

Carton	1
Package	10
Weight Per each	0.0119

### Uses, Certifications, and Standards

standard	UL and CSA
----------	------------