

# NEER Reducing Washers and Bushings

## RWN: Reducing Washer

### Applications

- Reduce knockout size on sheet metal box, enclosure or cabinet.

### Material/Finish

- Galvanized steel

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539, E61301
- CSA Standard: C22.2 No. 18.3
- cUL Listed: E61301
- NEMA: FB-1

#### Note:

- Two reducing washers are required for each knockout.



RWN

## RB: Reducing Bushing Flush Type

### Applications

- To reduce the trade size of a tapered entry.

### Features

- Threaded for rigid conduit and IMC.

### Material/Finish

- Steel/zinc plated

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-163167
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 70872
- NEMA: FB-1



RB

COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS

Commercial Products

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		Inside Diameter	Outside Diameter
3/4 x 1/2	<b>RWN-503</b>	0.88/22.4	1.44/36.6
1 x 1/2	<b>RWN-504</b>	0.88/22.4	1.75/44.5
1 x 3/4	<b>RWN-505</b>	1.11/28.2	1.75/44.5
1-1/4 x 1/2	<b>RWN-506</b>	0.88/22.4	2.19/55.6
1-1/4 x 3/4	<b>RWN-507</b>	1.11/28.2	2.19/55.6
1-1/4 x 1	<b>RWN-508</b>	1.37/34.8	2.19/55.6
1-1/2 x 1/2	<b>RWN-509</b>	0.88/22.4	2.50/63.5
1-1/2 x 3/4	<b>RWN-510</b>	1.11/28.2	2.50/63.5
1-1/2 x 1	<b>RWN-511</b>	1.37/34.8	2.50/63.5
1-1/2 x 1-1/4	<b>RWN-512</b>	1.73/43.9	2.50/63.5
2 x 1/4	<b>RWN-513</b>	0.88/22.4	3.00/76.2
2 x 3/4	<b>RWN-514</b>	1.11/28.2	3.00/76.2
2 x 1	<b>RWN-515</b>	1.37/34.8	3.00/76.2
2 x 1-1/4	<b>RWN-516</b>	1.73/43.9	3.00/76.2
2 x 1-1/2	<b>RWN-517</b>	1.98/50.3	3.00/76.2

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		Diameter	Height
3/4 x 1/2	<b>RB-2</b>	0.67/17.0	1.03/26.2
1 x 1/2	<b>RB-3</b>	0.71/18.0	1.28/32.5
1 x 3/4	<b>RB-4</b>	0.70/17.8	1.27/32.3
1-1/4 x 1/2	<b>RB-5</b>	0.71/18.0	1.62/41.1
1-1/4 x 3/4	<b>RB-6</b>	0.82/20.8	1.62/41.1
1-1/4 x 1	<b>RB-7</b>	0.82/20.8	1.63/41.4
1-1/2 x 1/2	<b>RB-8</b>	0.85/21.6	1.87/47.5
1-1/2 x 3/4	<b>RB-9</b>	0.85/21.6	1.88/47.8
1-1/2 x 1	<b>RB-10</b>	0.87/22.1	1.87/47.5
1-1/2 x 1-1/4	<b>RB-11</b>	0.85/21.6	1.87/47.5
2 x 1/2	<b>RB-12</b>	0.97/24.6	2.33/59.2
2 x 3/4	<b>RB-13</b>	0.98/24.9	2.34/59.4
2 x 1	<b>RB-14</b>	1.00/25.4	2.34/59.4
2 x 1-1/4	<b>RB-15</b>	0.97/24.6	2.34/59.4
2 x 1-1/2	<b>RB-16</b>	0.99/25.1	2.34/59.4