



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S10N06A07N 7.5KVA Buck Boost Transformer 1PH 120X240-16/32V

Eaton Corp

Catalog Number	S10N06A07N
Manufacturer	Eaton Corp
Description	Eaton General Purpose Encapsulated Transformer, Buck-Boost General-Purpose Encapsulated Transformer, Ep, Aluminum, Nema 3R, 178, 60 HZ, Single-Phase, 120 V, 240 V, 16/32 V, None, 115 °C Rise, 7.5 Kva, Indoor-Outdoor, 509B
Weight per unit	123.0 (lbs/each)
Product Category	20081031151214

Features

connection	509B
design	EP
dimensions	9.8900 IN X 10.3800 IN X 16.0000 IN
frame	178
Number of Phases	Single-phase
Primary Voltage	120 V, 240 V
Secondary Voltage	16/32 V

Descriptions

Description	7.5KVA BUCK BOOST TRANSFORMER 1PH 120X240-16/32V
extra long description	ETN S10N06A07N 7.5KVA Buck Boost TX
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.
Long Description	Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 178, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 7.5 KVA, indoor-outdoor, 509B
Product Type	7.5KVA Buck Boost TX 1PH 120X240-16/32V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786680103490
Manufacturers Part Number	S10N06A07N
UPC	786680103490

Taxonomies, Classifications, and Categories

Category Description	BUCK & BOOST TRANSFORMERS
Type	Encapsulated transformer

Packaging

Carton	1
Weight Per each	123

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Frequency Rating	60 Hz
standard	UL Listed
Temperature Rating	115 °C rise