

Specifications

Eaton S10N06P02P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 68P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 2 KVA, indoor-outdoor, 3C



Photo is representative



General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S10N06P02P
UPC	786680073618
PRODUCT LENGTH/DEPTH	6.32 in
PRODUCT HEIGHT	13.78 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	42 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	68P
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3C

Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	120 V, 240 V
SECONDARY VOLTAGE	16/32 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	2 kVA

Resources

CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S10N06P02P

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

