

Eaton S10N06P26P

Catalog Number: S10N06P26P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 57P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.25 KVA, indoor-outdoor, 3C

General specifications



| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton General purpose encapsulated transformer | S10N06P26P |
| | UPC |
| | 786680073649 |

| | |
|-----------------------------|-----------------------|
| Product Length/Depth | Product Height |
| 5.18 in | 9.34 in |

| | |
|----------------------|-----------------------|
| Product Width | Product Weight |
| 4.45 in | 13 lb |

| | |
|--|-----------------------|
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

57P

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

3C

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage

16/32 V

Temperature rise

115 °C rise

Volt ampere rating

0.25 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S10N06P26P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton S10N06P26P

Catalog Number: S10N06P26P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 57P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.25 KVA, indoor-outdoor, 3C

General specifications



| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton General purpose encapsulated transformer | S10N06P26P |
| | UPC |
| | 786680073649 |

| | |
|-----------------------------|-----------------------|
| Product Length/Depth | Product Height |
| 5.18 in | 9.34 in |

| | |
|----------------------|-----------------------|
| Product Width | Product Weight |
| 4.45 in | 13 lb |

| | |
|--|-----------------------|
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

57P

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

3C

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage

16/32 V

Temperature rise

115 °C rise

Volt ampere rating

0.25 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S10N06P26P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)