

Specifications



Photo is representative



Eaton S10N06P26P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 57P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.25 KVA, indoor-outdoor, 3C

General specifications

| | |
|----------------------|--|
| PRODUCT NAME | Eaton General purpose encapsulated transformer |
| CATALOG NUMBER | S10N06P26P |
| UPC | 786680073649 |
| PRODUCT LENGTH/DEPTH | 5.18 in |
| PRODUCT HEIGHT | 9.34 in |
| PRODUCT WIDTH | 4.45 in |
| PRODUCT WEIGHT | 13 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |



Powering Business Worldwide

| Physical Attributes | |
|---------------------|--|
| COIL MATERIAL | Aluminum |
| DESIGN | EP |
| ENCLOSURE | NEMA 3R |
| FRAME | 57P |
| TAP SIZE | None |
| TYPE | General-Purpose Encapsulated Transformer |
| WIRING CONNECTION | 3C |

| Miscellaneous | |
|---------------|----------------|
| WEATHERSHIELD | Indoor-Outdoor |

| Performance Ratings | |
|---------------------|--------------|
| FREQUENCY RATING | 60 Hz |
| PHASE | Single-phase |
| PRIMARY VOLTAGE | 120 V, 240 V |
| SECONDARY VOLTAGE | 16/32 V |
| TEMPERATURE RISE | 115 °C rise |
| VOLT AMPERE RATING | 0.25 kVA |

| Resources | |
|-------------------------------|---|
| CATALOGS | Commercial Distribution Transformers, Volume 2, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - S10N06P26P |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton S10N06P26P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 57P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.25 KVA, indoor-outdoor, 3C

General specifications

| | |
|----------------------|--|
| PRODUCT NAME | Eaton General purpose encapsulated transformer |
| CATALOG NUMBER | S10N06P26P |
| UPC | 786680073649 |
| PRODUCT LENGTH/DEPTH | 5.18 in |
| PRODUCT HEIGHT | 9.34 in |
| PRODUCT WIDTH | 4.45 in |
| PRODUCT WEIGHT | 13 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |

| Physical Attributes | |
|---------------------|--|
| COIL MATERIAL | Aluminum |
| DESIGN | EP |
| ENCLOSURE | NEMA 3R |
| FRAME | 57P |
| TAP SIZE | None |
| TYPE | General-Purpose Encapsulated Transformer |
| WIRING CONNECTION | 3C |

| Performance Ratings | |
|---------------------|--------------|
| FREQUENCY RATING | 60 Hz |
| PHASE | Single-phase |
| PRIMARY VOLTAGE | 120 V, 240 V |
| SECONDARY VOLTAGE | 16/32 V |
| TEMPERATURE RISE | 115 °C rise |
| VOLT AMPERE RATING | 0.25 kVA |

| Miscellaneous | |
|---------------|----------------|
| WEATHERSHIELD | Indoor-Outdoor |

| Resources | |
|-------------------------------|---|
| CATALOGS | Commercial Distribution Transformers, Volume 2, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - S10N06P26P |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

