

# Eaton S10N06P26P

Catalog Number: S10N06P26P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 57P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.25 KVA, indoor-outdoor, 3C

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S10N06P26P
	<b>UPC</b>
	786680073649

<b>Product Length/Depth</b>	<b>Product Height</b>
5.18 in	9.34 in

<b>Product Width</b>	<b>Product Weight</b>
4.45 in	13 lb

<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

57P

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3C

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

120 V, 240 V

### Secondary Voltage

16/32 V

### Temperature rise

115 °C rise

### Volt ampere rating

0.25 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S10N06P26P](#)