



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S12415 8W 6.5A19 CL Led E26 30K 120V

Satco

| | |
|------------------|--|
| Catalog Number | S12415 |
| Manufacturer | Satco |
| Description | 8 Watt Led A19 Lamp - Clear Medium Base 3000K 90 Cri 120 Volts |
| Weight per unit | 0.1200 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|--------------|-----------------|
| average life | 15000 |
| Base | Medium |
| beam angle | 320 |
| lumens | 800 |
| Material | Glass; Aluminum |
| Shape | A19 |
| Warranty | 3 Year Limited |

Material, Color, and Finish

| | |
|-------------------|-------|
| color temperature | 3000 |
| Finish | Clear |

Dimensions and Weight

| | |
|------|------|
| Size | 4.02 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 8W 6.5A19 CL LED E26 30K 120V |
| extra long description | SATCO S12415 8A19/CL/LED/E26/930/12 |
| Long Description | 8 Watt LED A19 Lamp - Clear Medium Base 3000K 90 CRI 120 Volts |
| Product Type | 8A19/CL/Led/E26/930/120V |
| Special Features | Lawful for sale in California ; Dimmable: Yes - Dimmable ; Color temperature: Soft White ; Incandescent equivalent: 60W ; Material: Aluminum and Glass ; Location rating: Wet ; Enclosed fixture rated: Yes ; Style: Vintage ; Operating temperature: -20C (-4F) to a maximum of 45C (113F) ; Warranty: 3 Year Limited |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923124150 |
| Manufacturers Part Number | S12415 |
| UPC | 045923124150 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
| Type | A19 |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight | 0.07 |
| Weight Per each | 0.12 |

Uses, Certifications, and Standards

| | |
|-----------------------|---|
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |
| standard | cULus Listed |