



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S12415 8W 6.5A19 CL Led E26 30K 120V

Satco

Catalog Number	S12415
Manufacturer	Satco
Description	8 Watt Led A19 Lamp - Clear Medium Base 3000K 90 Cri 120 Volts
Weight per unit	0.1200 (lbs/each)
Product Category	Lighting

### Features

average life	15000
Base	Medium
beam angle	320
lumens	800
Material	Glass; Aluminum
Shape	A19
Warranty	3 Year Limited

### Material, Color, and Finish

color temperature	3000
Finish	Clear

### Dimensions and Weight

Size	4.02
------	------

### Descriptions

Description	8W 6.5A19 CL LED E26 30K 120V
extra long description	SATCO S12415 8A19/CL/LED/E26/930/12
Long Description	8 Watt LED A19 Lamp - Clear Medium Base 3000K 90 CRI 120 Volts
Product Type	8A19/CL/Led/E26/930/120V
Special Features	Lawful for sale in California ; Dimmable: Yes - Dimmable ; Color temperature: Soft White ; Incandescent equivalent: 60W ; Material: Aluminum and Glass ; Location rating: Wet ; Enclosed fixture rated: Yes ; Style: Vintage ; Operating temperature: -20C (-4F) to a maximum of 45C ( 113F) ; Warranty: 3 Year Limited

### Manufacturer Information

Brand	Satco
GTIN	00045923124150
Manufacturers Part Number	S12415
UPC	045923124150



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	A19

## Packaging

Carton	1
Weight	0.07
Weight Per each	0.12

## Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus Listed