



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S12417 8W Led A19 40K Clear 800LM

Satco

Catalog Number	S12417
Manufacturer	Satco
Description	8 Watt Led A19 Lamp - Clear Medium Base 4000K 90 Cri 120 Volts
Weight per unit	1.5 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	Medium
beam angle	320
lumens	800
Material	Glass; Aluminum
Shape	A19
Warranty	3 Year Limited

Material, Color, and Finish

color temperature	4000
Finish	Clear

Dimensions and Weight

Size	4.02
------	------

Descriptions

Description	8W LED A19 40K CLEAR 800LM
extra long description	SATCO S12417 8A19/CL/LED/E26/940/12
Long Description	8 Watt LED A19 Lamp - Clear Medium Base 4000K 90 CRI 120 Volts
Product Type	8A19/CL/Led/E26/940/120V
Special Features	Lawful for sale in California ; Dimmable: Yes - Dimmable ; Color temperature: Cool White ; Incandescent equivalent: 60W ; Material: Aluminum and Glass ; Location rating: Wet ; Enclosed fixture rated: Yes ; Style: Vintage ; Operating temperature: -20C (-4F) to a maximum of 45C (113F) ; Warranty: 3 Year Limited

Manufacturer Information

Brand	Satco
GTIN	00045923124174
Manufacturers Part Number	S12417
UPC	045923124174



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	A19

Packaging

Carton	1
Weight	0.07
Weight Per each	1.5

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus Listed