



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S126V 12-10 Awg Vinyl Insulated Spade #6 Stud

Nsi Industries

Catalog Number	S126V
Manufacturer	Nsi Industries
Description	Tin-Plated Copper Spade Terminal Is Insulated With Vinyl and Has An Open Tongue End For Rapid Insertion On The Mounting Screw. Used For Wire Termination In Applications With #6 Stud and 12-10 Awg.
Weight per unit	0.2020 (lbs/each)
Product Category	Tools & Testers

Features

Material	Copper, PVC
Number of Terminals	1
Terminal Size	# 6
Voltage Rating	300V
Warranty	1 YEAR
Wire Size	12-10 AWG

Material, Color, and Finish

Color	Yellow
Finish	Tin Plated

Descriptions

Description	12-10 AWG VINYL INSULATED SPADE #6 STUD
extra long description	NSI S12-6V 12-10 Bare Locking Spade
Features	12-10 AWG Vinyl Insulated Spade #6 Stud, 50 Per Pack
Long Description	Tin-plated Copper Spade terminal is insulated with vinyl and has an open tongue end for rapid insertion on the mounting screw. Used for wire termination in applications with #6 Stud and 12-10 AWG.
Product Type	12-10 Bare Locking Spade-Bulk
Special Features	Vinyl Insulated Spade Terminal 12-10 AWG - 50 Pack

Manufacturer Information

Brand	NSi
GTIN	00662381062901
Manufacturers Part Number	S12-6V
UPC	662381062901

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Vinyl Insulated Spade Terminal



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.202

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	75 C
standard	cULus