



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S13136 42W Led Hid Replacement ED28 Shape 5K Mog Ex 6000L *Satco*

Catalog Number	S13136
Manufacturer	Satco
Description	42 Watt Led Hid Replacement - ED28 - 5000K - Mogul Extended Base - 120-277 Volts - Type B Ballast Bypass
Weight per unit	0.7400 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	Mogul Extended
beam angle	360
lumens	6k
Material	Glass; Metal
Shape	ED28
Warranty	3 Year Limited - 12 hr per day

Material, Color, and Finish

color temperature	5000
Finish	white

Dimensions and Weight

Size	8.54
------	------

Descriptions

Description	42W LED HID REPLACEMENT ED28 SHAPE 5K MOG EX 6000L
extra long description	SATCO S13136 42W/LED/HID/ED28/850/E
Long Description	42 Watt LED HID Replacement - ED28 - 5000K - Mogul Extended Base - 120-277 Volts - Type B Ballast Bypass
Product Type	42W/Led/Hid/ED28/850/Ex39
Special Features	Lawful for sale in California ; Volts: 120V-277V ; Non-Dimmable ; MOL: 8.54 in. ; MOD: 3.54 in. ; Warranty: 3 Year Limited - 12 hours per day ; Enclosure Rated: Yes ; Material: Glass, Metal ; IP Rating: IP65 ; Operating Temperature: -30C (-22F) to a maximum of +65C (+149F)



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923131363
Manufacturers Part Number	S13136
UPC	045923131363

Taxonomies, Classifications, and Categories

Category Description	LED ELLIPTICAL E SHAPE LAMPS
Type	HID Replacements

Packaging

Carton	1
Package	12
Weight	0.49
Weight Per each	0.74

Uses, Certifications, and Standards

Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
standard	cULus