



S1940

LU250
250 watt; High Pressure Sodium HID; Mogul base; ET18; Clear;
22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1940

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S1940	045923019401	250	ET18	Mogul	E39	S50	LU250

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	9 5/8"	2.25"	24000	28000	2100	12	22

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S1940

LU250
250 watt; High Pressure Sodium HID; Mogul base; ET18; Clear;
22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1940

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S1940	045923019401	250	ET18	Mogul	E39	S50	LU250

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	9 5/8"	2.25"	24000	28000	2100	12	22

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

