



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S201K16 1P 480V 16A Breaker

Industrial Connections &

Catalog Number	S201K16
Manufacturer	Industrial Connections &
Description	Miniature Circuit Breaker, K Curve, 16 A, Thermal Magnetic Tripping Mechanism, Screw Terminal, Din Rail Mount, 277/Y480 V Ac;60/110 V DC, 50/60 HZ, +55 °C Operating Temperature, -25 °C Operating Temperature, 88 MM Overall Height, 69 MM Overall Length, 17.5 MM Overall Width, 0.29 LB
Weight per unit	0.2900 (lbs/each)
Product Category	1 Pole Supplementary Protector

Features

amperage rating	16 OZ
Poles	1 PH
Trip Type	OUTSIDE CORNER FITTING, OUTSIDE CORNER FITTING TYPE; ABS PLASTIC MATERIAL; 1.5 INCH L X 0.91 INCH W X 0.6 INCH H SIZE; WHITE FINISH; PAN-WAY LD10 SERIES NON-METALLIC SURFACE RACEWAY USED ON; UL, CE APPROVAL; 10 STANDARD PACKAGE; PAN-WAY[R] BRAND

Dimensions and Weight

Height	88 Millimeters
Length	69 Millimeters
Width	17.5 Millimeters

Descriptions

Description	1P 480V 16A BREAKER
extra long description	ABB S201-K16 LEGACY SEE REPLACEMENT
Special Features	High performance MCB provides compact supplementary, energy limiting, circuit protection

Manufacturer Information

GTIN	00662019168531
sub brand	System pro M compact
UPC	662019168531

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	High Performance MCB Provides Compact Supplementary, Energy Limiting, Circuit Protection



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.29

Uses, Certifications, and Standards

Application	For use as a supplemental protection device
Operating Temperature	-25 to +55 Degrees Celcius
standard	UL 1077, CSA 22.2 No. 235, IEC 60898