



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S202K16 2P 480V 16A Breaker

Industrial Connections &

Catalog Number	S202K16
Manufacturer	Industrial Connections &
Description	Miniature Circuit Breaker, 16 A, Thermal Magnetic Tripping Mechanism, Screw Terminal, Din Rail Mount, 277/Y480 V Ac;60/110 V DC, 50/60 HZ, +55 °C Operating Temperature, -25 °C Operating Temperature, 88 MM Overall Height, 69 MM Overall Length, 35 MM Overall Width, 0.57 LB
Weight per unit	0.5700 (lbs/each)
Product Category	2 Pole Supplementary Protector

Features

amperage rating	16 lbs./100ft
Poles	2 in
Trip Type	OUTSIDE CORNER FITTING, OUTSIDE CORNER FITTING TYPE; ABS PLASTIC MATERIAL; 1.5 INCH L X 0.91 INCH W X 0.6 INCH H SIZE; WHITE FINISH; PAN-WAY LD10 SERIES NON-METALLIC SURFACE RACEWAY USED ON; UL, CE APPROVAL; 10 STANDARD PACKAGE; PAN-WAY[R] BRAND

Dimensions and Weight

Height	88 Millimeters
Length	69 Millimeters
Width	35 W

Descriptions

Description	2P 480V 16A BREAKER
extra long description	ABB S202-K16 LEGACY SEE REPLACEMENT
Special Features	High performance MCB provides compact supplementary, energy limiting, circuit protection

Manufacturer Information

GTIN	00662019170923
sub brand	System pro M compact
UPC	662019170923

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	High Performance MCB Provides Compact Supplementary, Energy Limiting, Circuit Protection

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.57

Uses, Certifications, and Standards

Application	For use as a supplemental protection device
Operating Temperature	-25 to +55 Degrees Celcius
standard	UL 1077, CSA 22.2 No. 235, IEC 60898